

CIRCUIT: SPDT
CONTACT CONFIGURATION




SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
DN	DFF	<DN>
2-3	DPEN	2-1

()=Momentary

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 3A @120VAC, OR 28VDC
1A @250VAC
5. FIXED TERMINAL/MOVING CONTACT MATERIAL:
COPPER ALLOY w/SILVER PLATING
6. ELECTRIC LIFE: 30,000 mke-and-brek cycles
at full load.
7. INSULATION RESISTANCE: 1,000 M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP. -30°C to +85°C
10. ▲ DESIGNATE MAJOR FEATURE
11. 2002/95/EC (ROHS) COMPLANT

RECOMMENDED P.C.B. LAYOUT



REV.	ECN No.	DESCRIPTION	DATE	CHKD
A	12275	RELEASED	6/27/02	CJB

TITLE				
400 MSP-5 R1 (BLK) M71 QE				
E-SWITCH® LAMB INDUSTRIES				

REV.	ECN No.	DESCRIPTION	DATE	CHKD
A	12275	RELEASED	6/27/02	CJB

SCALE	DATE	DR	DWG	REV
2:1	6/27/02	CJB	T415113	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED