








▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	NONE	ON
2-3; 5-6	NONE	2-1; 5-4



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACTS: GOLD PLATED
- RATING: 0.4 VA max. @ 20V AC OR DC max.
- CONTACT RESISTANCE: <100 MILLI-OHM
- ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES.
- INSULATION RESISTANCE: 500 MEGA-OHM min.
- DIELECTRIC STRENGTH: 500 V RMS @SEA LEVEL.
- OPERATING TEMP.: -30°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-102000	REMOVED THE IP SEAL RATING	06/09/23	JS	TITLE 400UDP1L1BLKM6RE				000025513
					SCALE 5/2	DATE 8/11/2015	DR rc	DWG T480004	REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED