







SWITCH FUNCTION	
POS. 1	POS. 2
	
ON	(ON)
1-3, 4-6	1-2, 4-5

(ON)=MOMENTARY



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 4. CONTACT MATERIAL: GOLD
 5. RATING: 0.4VA MAX. @ 20 VAC OR VDC MAX.
 6. ELECTRIC LIFE: 6,000 MAKE-AND-BREAK CYCLES AT FULL LOAD
 7. MECHANICAL LIFE: 50,000 CYCLES
 8. INSULATION RESISTANCE: 1,000 MΩ MIN.
 9. ACTUATION FORCE: 800 ± 200gf
 10. TRAVEL: 1.0 ± 0.2mm
 11. CONTACT RESISTANCE: 20 mΩ MAX.
TYPICAL @ 2-4 VDC
 12. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL.
 13. OPERATING TEMP.: -40°C to 85°C
 14. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
E	ECO-102944	700 SERIES UPDATE	09/24/24	JS	TITLE 700DP7B11M1RE				000025749
					SCALE 2:1	DATE 1/27/2006	DR PH	DWG T711063	REV E

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED