

P.C. MOUNTING

▲ SWITCH FUNCTION

POS. 1	POS. 2
OFF	(ON)
OPEN	1-3






(ON)=MOMENTARY



CIRCUIT: SPST

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: GOLD
5. RATING: 0.4 AMPS @ 20V (AC or DC)
6. ELECTRIC LIFE: 30,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
9. TOTAL TRAVEL: 0.80 mm
10. OPERATING TEMP.: -30°C to 85°C
11. ▲ DENOTES CRITICAL PARAMETER.



B	18489	REVISE DIMENSION FOR CAP HEIGHT	4/15/09	BLR
A	18474	RELEASED FOR PRODUCTION	4/13/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE 800SP9B10M61REC1WHT

SCALE 2:1

DATE 4/15/2009

DR BLR

DWG XT0150P

REV B