




▲ CAP  
COLOR: BLACK

▲ SWITCH FUNCTION



| POS. 1 | POS. 2 |
|--------|--------|
|        |        |
| ON     | (ON)   |
| 1-3    | 1-2    |

(ON) = MOMENTARY



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 1 AMP @ 250 VAC  
3 AMP @ 120 VAC or 28VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.
11. HARDWARE TO BE SHIPPED BULK  
T100000 - HEXNUT - QTY 2  
T100011 - LOCKWASHER - QTY 1  
T100015 - LOCKRING - QTY 1



E-SWITCH®

|     |        |                         |         |    |
|-----|--------|-------------------------|---------|----|
| A   | 23892  | RELEASED FOR PRODUCTION | 5/16/19 | MW |
| REV | PCR NO | DESCRIPTION             | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|                            |                |       |             |       |
|----------------------------|----------------|-------|-------------|-------|
| TITLE 700SP7B10M52QEHC1BLK |                |       |             |       |
| SCALE 2:1                  | DATE 5/16/2019 | DR MW | DWG XT0177P | REV A |