



APFA2507LQBDSEEZGKC

2.5 x 0.7 mm Right Angle SMD Chip LED Lamp

DESCRIPTIONS

- The Blue source color devices are made with InGaN Light Emitting Diode
- The Hyper Red source color devices are made with AlGaNp on GaAs substrate Light Emitting Diode
- The Green source color devices are made with InGaN on Sapphire Light Emitting Diode
- Electrostatic discharge and power surge could damage the LEDs
- It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- All devices, equipments and machineries must be electrically grounded

FEATURES

- 2.5 x 1.0 x 0.7 mm right angle SMD LED, 0.7 mm thickness
- Low power consumption
- Wide viewing angle
- Ideal for backlight and indicator
- Package: 3000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- Tinned pads for improved solderability
- RoHS compliant

APPLICATIONS



- Backlight
- Status indicator
- Home and smart appliances
- Wearable and portable devices
- Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices




PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units : mm; tolerance : ± 0.1)



Notes:

- All dimensions are in millimeters (inches).
- Tolerance is $\pm 0.15(0.006")$ unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
- The device has a single mounting surface. The device must be mounted according to the specifications.
- For right angle SMD LEDs, the solder stencil should be at least 5mil in thickness, to prevent poor solder wetting due to insufficient solder paste.

SELECTION GUIDE

| Part Number | Emitting Color (Material) | Lens Type | I _v (mcd) @ 2mA ^[2] | | Viewing Angle ^[1] |
|---------------------|---------------------------|-------------|---|------|------------------------------|
| | | | Min. | Typ. | |
| APFA2507LQBDSEEZGKC | Blue (InGaN) | Water Clear | 4 | 10 | 130° |
| | Hyper Red (AlGaNp) | | 6 | 10 | |
| | Green (InGaN) | | 50 | 100 | |

Notes:

- $\theta/2$ is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
- Luminous intensity / luminous flux: $\pm 15\%$.
- Luminous intensity value is traceable to CIE127-2007 standards.

ELECTRICAL / OPTICAL CHARACTERISTICS at $T_A=25^\circ\text{C}$

| Parameter | Symbol | Emitting Color | Value | | Unit |
|---|-------------------------------------|----------------------------|----------------------|-------------------|----------------------------|
| | | | Typ. | Max. | |
| Wavelength at Peak Emission $I_F = 2\text{mA}$ | λ_{peak} | Blue Hyper Red Green | 460 630 515 | - | nm |
| Dominant Wavelength $I_F = 2\text{mA}$ | $\lambda_{\text{dom}}^{[1]}$ | Blue Hyper Red Green | 465 621 525 | - | nm |
| Spectral Bandwidth at 50% Φ REL MAX $I_F = 2\text{mA}$ | $\Delta\lambda$ | Blue Hyper Red Green | 25 20 35 | - | nm |
| Forward Voltage $I_F = 2\text{mA}$ | $V_F^{[2]}$ | Blue Hyper Red Green | 2.65 1.8 2.65 | 3.1 2.1 3.1 | V |
| Reverse Current ($V_R = 5\text{V}$) | I_R | Blue Hyper Red Green | - | 50 10 50 | μA |
| Temperature Coefficient of λ_{peak} $I_F = 2\text{mA}$, $-10^\circ\text{C} \leq T \leq 85^\circ\text{C}$ | $\text{TC}_{\lambda_{\text{peak}}}$ | Blue Hyper Red Green | 0.04 0.13 0.05 | - | $\text{nm}/^\circ\text{C}$ |
| Temperature Coefficient of λ_{dom} $I_F = 2\text{mA}$, $-10^\circ\text{C} \leq T \leq 85^\circ\text{C}$ | $\text{TC}_{\lambda_{\text{dom}}}$ | Blue Hyper Red Green | 0.03 0.06 0.03 | - | $\text{nm}/^\circ\text{C}$ |
| Temperature Coefficient of V_F $I_F = 2\text{mA}$, $-10^\circ\text{C} \leq T \leq 85^\circ\text{C}$ | TC_V | Blue Hyper Red Green | -3.0 -1.9 -3.0 | - | $\text{mV}/^\circ\text{C}$ |

Notes:

1. The dominant wavelength (λ_d) above is the setup value of the sorting machine. (Tolerance $\lambda_d: \pm 1\text{nm}$.)
2. Forward voltage: $\pm 0.1\text{V}$.
3. Wavelength value is traceable to CIE127-2007 standards.
4. Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

ABSOLUTE MAXIMUM RATINGS at $T_A=25^\circ\text{C}$


| Parameter | Symbol | Value | | | Unit |
|--|--------------------------|------------|-----------|-------|---------------------------|
| | | Blue | Hyper Red | Green | |
| Power Dissipation | P_D | 120 | 75 | 102.5 | mW |
| Reverse Voltage | V_R | 5 | 5 | 5 | V |
| Junction Temperature | T_j | 115 | 115 | 115 | $^\circ\text{C}$ |
| Operating Temperature | T_{op} | -40 to +85 | | | $^\circ\text{C}$ |
| Storage Temperature | T_{stg} | -40 to +85 | | | $^\circ\text{C}$ |
| DC Forward Current | I_F | 30 | 30 | 25 | mA |
| Peak Forward Current | $I_{\text{FP}}^{[1]}$ | 150 | 195 | 150 | mA |
| Electrostatic Discharge Threshold (HBM) | - | 250 | 3000 | 450 | V |
| Thermal Resistance (Junction / Ambient) | $R_{\text{th JA}}^{[2]}$ | 580 | 670 | 560 | $^\circ\text{C}/\text{W}$ |
| Thermal Resistance (Junction / Solder point) | $R_{\text{th JS}}^{[2]}$ | 460 | 570 | 440 | $^\circ\text{C}/\text{W}$ |

Notes:


1. 1/10 Duty Cycle, 0.1ms Pulse Width.
2. $R_{\text{th JA}}, R_{\text{th JS}}$ Results from mounting on PC board FR4 (pad size $\geq 16\text{ mm}^2$ per pad).
3. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

TECHNICAL DATA





RELATIVE INTENSITY vs. WAVELENGTH







SPATIAL DISTRIBUTION







BLUE




HYPER RED



GREEN




REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS




Notes:

1. Don't cause stress to the LEDs while
2. The maximum number of reflow solder
3. Reflow soldering is recommended. O
cause damage to the product.


TAPE SPECIFICATIONS (units : mm)



REEL DIMENSION (units : mm)



PACKING & LABEL SPECIFICATIONS



PRECAUTIONARY NOTES

PRECAUTIONARY NOTES

1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
6. All design applications should refer to Kingbright application notes available at <https://www.KingbrightUSA.com/ApplicationNotes>