

APGB0607G22R23C

0.65 x 0.65 x 0.25 mm Bi-Color Surface Mount LED

DESCRIPTIONS

- The Green source color devices are made with InGaN on Sapphire Light Emitting Diode
- The Hyper-Red source color devices are made with AlGaNp on GaAs substrate Light Emitting Diode
- Electrostatic discharge and power surge could damage the LEDs
- It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- All devices, equipments and machineries must be electrically grounded

FEATURES

- 0.65 mm x 0.65 mm SMD LED, 0.25 mm thickness
- Low power consumption
- Package: 4000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- RoHS compliant

APPLICATIONS


- Backlight
- Status indicator
- Home and smart appliances
- Wearable and portable devices
- Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices




PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units : mm; tolerance : ± 0.1)



Notes:

- All dimensions are in millimeters (inches).
- Tolerance is $\pm 0.1(0.004")$ unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
- The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

| Part Number | Emitting Color (Material) | Lens Type | I _v (mcd) @ 5mA ^[2] | | Viewing Angle ^[1] |
|-----------------|---------------------------|-------------|---|------|------------------------------|
| | | | Min. | Typ. | |
| APGB0607G22R23C | Green (InGaN) | Water Clear | 50 | 200 | 140° |
| | Hyper Red (AlGaNp) | | *50 | *200 | |
| | | | 30 | 75 | |
| | | | *8 | *25 | |
| | | | | | |

Notes:

- $\theta/2$ is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
- Luminous intensity / luminous flux: +/-15%.

* Luminous intensity value is traceable to CIE127-2007 standards.

ELECTRICAL / OPTICAL CHARACTERISTICS at $T_A=25^\circ\text{C}$

| Parameter | Symbol | Emitting Color | Value | | Unit |
|---|------------------------------|--------------------|--------------|------------|----------------------------|
| | | | Typ. | Max. | |
| Wavelength at Peak Emission $I_F = 5\text{mA}$ | λ_{peak} | Green Hyper Red | 515 632 | - | nm |
| Dominant Wavelength $I_F = 5\text{mA}$ | $\lambda_{\text{dom}}^{[1]}$ | Green Hyper Red | 525 624 | - | nm |
| Spectral Bandwidth at 50% Φ REL MAX $I_F = 5\text{mA}$ | $\Delta\lambda$ | Green Hyper Red | 30 20 | - | nm |
| Forward Voltage $I_F = 5\text{mA}$ | $V_F^{[2]}$ | Green Hyper Red | 2.85 1.95 | 3.3 2.3 | V |
| Reverse Current ($V_R = 5\text{V}$) | I_R | Green Hyper Red | - | 50 10 | μA |
| Temperature Coefficient of λ_{peak} $I_F = 5\text{mA}$, $-10^\circ\text{C} \leq T \leq 85^\circ\text{C}$ | $TC_{\lambda_{\text{peak}}}$ | Green Hyper Red | 0.05 0.13 | - | $\text{nm}/^\circ\text{C}$ |
| Temperature Coefficient of λ_{dom} $I_F = 5\text{mA}$, $-10^\circ\text{C} \leq T \leq 85^\circ\text{C}$ | $TC_{\lambda_{\text{dom}}}$ | Green Hyper Red | 0.03 0.06 | - | $\text{nm}/^\circ\text{C}$ |
| Temperature Coefficient of V_F $I_F = 5\text{mA}$, $-10^\circ\text{C} \leq T \leq 85^\circ\text{C}$ | TC_V | Green Hyper Red | -3.0 -1.9 | - | $\text{mV}/^\circ\text{C}$ |

Notes:

1. The dominant wavelength (λ_{d}) above is the setup value of the sorting machine. (Tolerance λ_{d} : $\pm 1\text{nm}$.)
2. Forward voltage: $\pm 0.1\text{V}$.
3. Wavelength value is traceable to CIE127-2007 standards.
4. Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

ABSOLUTE MAXIMUM RATINGS at $T_A=25^\circ\text{C}$


| Parameter | Symbol | Value | | Unit |
|--|--------------------------|-------------|-----------|--------------------|
| | | Green | Hyper Red | |
| Power Dissipation | $P_D^{[1]}$ | 35 | | mW |
| Reverse Voltage | V_R | 5 | 5 | V |
| Junction Temperature | T_j | 115 | 115 | $^\circ\text{C}$ |
| Operating Temperature | T_{op} | -40 To +85 | | $^\circ\text{C}$ |
| Storage Temperature | T_{stg} | -40 To +100 | | $^\circ\text{C}$ |
| DC Forward Current | $I_F^{[2]}$ | 10 | 10 | mA |
| Peak Forward Current | $I_{FP}^{[3]}$ | 50 | 40 | mA |
| Electrostatic Discharge Threshold (HBM) | - | 450 | 3000 | V |
| Thermal Resistance (Junction / Ambient) | $R_{\text{th JA}}^{[4]}$ | 780 | 650 | $^\circ\text{C/W}$ |
| Thermal Resistance (Junction / Solder point) | $R_{\text{th JS}}^{[4]}$ | 650 | 480 | $^\circ\text{C/W}$ |

Notes:


1. Within 35mW when multiple chips are lightened
2. The maximum ratings are valid for the case of lighting a single chip
When two chips are lit at the same time, each chip should be driven at a current lower than 50% of the absolute maximum ratings
3. Duty Cycle $\leq 1/20$, Pulse Width = 1ms.
4. $R_{\text{th JA}}, R_{\text{th JS}}$ Results from mounting on PC board FR4 (pad size $\geq 16\text{ mm}^2$ per pad).
5. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

TECHNICAL DATA





RELATIVE INTENSITY vs. WAVELENGTH







SPATIAL DISTRIBUTION




GREEN



HYPER RED




REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS





Notes:

1. Don't cause stress to the LEDs while it is exposed to high temperature.
2. The maximum number of reflow soldering passes is 2 times.
3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

TAPE SPECIFICATIONS (units : mm)



PACKING & LABEL SPECIFICATIONS



PRECAUTIONARY NOTES

1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
6. All design applications should refer to Kingbright application notes available at <https://www.KingbrightUSA.com/ApplicationNotes>