




SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)

2-1 2-3

(ON)=MOMENTARY



NOTE:
 1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X = ± 0.4
 X.XX = ± 0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 ▲4. CONTACT/TERMINALS: SILVER PLATED
 5. RATING: 1A @ 250 VAC
 3A @ 120 VAC or 28 VDC
 6. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
 7. MECHANICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES
 8. CONTACT RESISTANCE: 20mΩ MAX. INITIAL @ 2-4VDC
 100mA FOR BOTH GOLD AND SILVER CONTACTS
 9. INSULATION RESISTANCE: 1,000MΩ MIN.
 10. ELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
 11. OPERATING TEMP.: -40°C to 85°C
 12. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®			OBJECT ID
F	ECO-103159	Print update	12/30/24	MW				000025895
					TITLE 800SP8B9M1QE			
					SCALE 2:1			
		THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED	DATE	5/29/1996	DR	MM	DWG	T822013
					REV			F