






SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-3

(ON)=MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACTS/TERMINALS: SILVER PLATED
- RATING: 1A @ 250 VAC
3A @ 120 VAC or 28 VDC
- ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
- MECHANICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES
- CONTACT RESISTANCE: 20m Ω MAX. INITIAL @ 2-4VDC 100mA
FOR BOTH GOLD AND SILVER CONTACTS
- INSULATION RESISTANCE: 1,000M Ω MIN.
- ELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL
- OPERATING TEMP.: -40°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-103116	print update	12/25/24	MW	TITLE 800SP9B10M6QE				000025901
					SCALE 2:1	DATE 6/17/2011	DR BMA	DWG T822023	REV C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED