






SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-3

(ON) = MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACTS/TERMINALS: SILVER PLATED
- RATING: 1A @ 250 VAC
3A @ 120 VAC OR 28 VDC
- ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
- MECHANICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES
- CONTACT RESISTANCE: 20m Ω MAX. INITIAL @ 2-4VDC 100mA
- INSULATION RESISTANCE: 1,000M Ω MIN.
- DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
- OPERATING TEMP.: -40°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®					OBJECT ID 000025846	
G	ECO-103132	print update	12/26/24	MW							
					TITLE 800SP9B5M2QE						
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 2:1	DATE 6/8/2011	DR BMA	DWG T811004	REV G		