







P.C. MOUNTING





| SWITCH FUNCTION         |        |                         |
|-------------------------|--------|-------------------------|
| POS. 1                  | POS. 2 | POS. 3                  |
|                         |        |                         |
| ON                      | NONE   | ON                      |
| 2-3, 5-6,<br>8-9, 11-12 | N/A    | 2-1, 5-4,<br>8-7, 11-10 |



CIRCUIT: 4PDT

## NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- PLATING MATERIAL: SILVER
- RATING: 5A@120VAC OR 28VDC  
2A@250VAC WITH RESISTIVE LOADS
- ELECTRIC LIFE: 40,000 make-and-break cycles at full load.
- INSULATION RESISTANCE: 1,000MΩ min.
- DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
- OPERATING TEMP.: -40°C to 85°C
- ▲ DENOTES CRITICAL PARAMETER.

E-SWITCH  
MARKING ON  
OPPOSITE SIDEEPOXY  
SEAL

| REV | ECO NO     | DESCRIPTION  | DATE     | BY | E-SWITCH®            |           |    |         | OBJECT ID |
|-----|------------|--------------|----------|----|----------------------|-----------|----|---------|-----------|
| C   | ECO-101559 | PRINT UPDATE | 02/03/23 | JS | TITLE 1004P1T1B1M7QE |           |    |         | 000024458 |
|     |            |              |          |    | SCALE                | DATE      | DR | DWG     | REV       |
|     |            |              |          |    | 2:1                  | 4/25/2003 | AR | T141005 | C         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED