





PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040005	D16EES11
2	1	F050315	50-003-15 TRANSPARENT FLAT WHITE LENS
3	1	F050431	50-004-31 6V WHITE LED

PANEL MOUNTING

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. RATING: 5A @ 250 VAC
6A @ 24 VDC
8A @ 125 VAC
5. ELECTRIC LIFE: 50,000 CYCLES
6. INSULATION RESISTANCE: 1,000 MΩ MIN.
7. OPERATING TEMP.: -20°C to 55°C
8. LAMP VOLTAGE: 6VDC LED
9. ▲ DENOTES CRITICAL PARAMETER.
10. 2002/05/EC (ROHS) COMPLIANT.
11. PANEL THICKNESS: 0.5-5.0mm
12. TRAVEL: 3.0mm FULL, 2.0mm LATCH
13. SEAL RATING: IP40

A	21590	RELEASED FOR PRODUCTION	9/22/14	EBP
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE	DATE	DR	DWG	REV
	9/22/2014	EBP	XF0894P	A

 E-SWITCH®