




| ITEM | QTY | PART NUMBER | DESCRIPTION |
|------|-----|-------------|-----------------------------------|
| 1 | 1 | F040021 | D16EES13 |
| 2 | 1 | F050314 | 50-003-14 LENS, SQUARE, FLAT, RED |
| 3 | 1 | F050406 | 50-004-06 Bulb, 48V AC/DC 25mA |



- NOTE:
1. ALL DIMENSIONS IN MM [INCH].
 2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
 3. TERMINAL NUMBERS FOR REF ONLY.
 4. RATING: 5A @ 250VAC UL, VDE
8A @ 125VAC UL, VDE
6A @ 24VDC
0.2A @ 250VDC
 5. ELECTRICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD min.
 6. INSULATION RESISTANCE: 1,000 MEGA-OHM min.
 7. OPERATING TEMP.: -25°C to +55°C
 - ▲ 8. LAMP VOLTAGE: 48V AC/DC 25mA INCANDESCENT
 9. PANEL THICKNESS = 0.5mm to 5.0 mm
 10. ▲ DENOTES CRITICAL PARAMETER.
 11. PACKAGE: BOX / 20 PIECES PER BOX
 12. DEGREE OF PROTECTION: IP40
 13. TRAVEL: 3.00 mm FULL TRAVEL, 2.0 mm LATCHING
 14. 2011/65/EU (ROHS) COMPLIANT



| | | | | |
|-----|--------|-------------------------|----------|----|
| A | 22637 | RELEASED FOR PRODUCTION | 12/13/16 | MW |
| REV | PCR NO | DESCRIPTION | DATE | BY |

| | | | | |
|--------------------|-----------------|-------|-------------|-------|
| TITLE D16EES13DRED | | | | |
| SCALE 3:2 | DATE 12/13/2016 | DR MW | DWG XF0912P | REV A |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED