







RECOMMENDED PANEL MOUNTING



CIRCUIT: DPDT

SWITCH FUNCTION ▲			
PDS. 1	PDS. 2	PDS. 3	
2-3,5-6	2-3,5-4	2-1,5-4	


NOTES:

() =Momentary

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 4VA Max. @ 20V Max(ACor DC)
5. FIXED TERM. & MOVING CONTACT:
Copper Alloy w/Gold Plate.
6. ELECTRICAL LIFE: 50,000 make-and-break cycles at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1000V RMS @sea level
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.

C	14320	CORRECT ACTUATOR HEIGHT	9/15/04	AR
B	13147	7.55 WAS 7.11	5/22/03	AR
A	12802	RELEASED FOR PRODUCTION	2/7/03	RC
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E-SWITCH®

100DP4T6B11VSSRE

TITLE		DATE		DR		DWG		REV	
SCALE		2/1		2/7/03		CJB		T102314	
SCALE		2/1		2/7/03		CJB		T102314	
DATE		2/7/03		CJB		T102314		C	