






CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING



NOTE:

1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
- ▲ 4. CONTACT MATERIAL: GOLD
5. CONTACT RATING: 150MILLIAMP, 250VAC/DC
350MILLIAMP, 110VAC/DC
6. CONTACT RATING (NON-SWITCHING) 5A
7. OPERATING FORCE 425 $\pm$ 100CM/STANDARD
8. OPERATING TEMP: -30°C to 85°C
- ▲ 9. CIRCUIT 3P: 4 POSITION 30° INDEX.
10. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL.
- ▲ 11. HARDWARE SUPPLIED ON SWITCH:
LOCKWASHER, HEXNUT, & STOPRING.
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2011/65/EU(ROHS) COMPLIANT
- ▲ 14. PACKAGE: TRAY/462 PIECES PER



C	23292	update print	4/2/18	MW
B	17928	add stopring to note 11	1/17/08	TN
A	16993	RELEASED FOR PRODUCTION	2/14/07	TN
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE KC34B30.001NPF

SCALE 3:2	DATE 2/14/2007	DR TN	DWG G510359	REV C
--------------	-------------------	----------	----------------	----------