





SCHEMATIC
ON - (ON)
SPDT ILLUMINATED

() DENOTED MOMENTARY FUNCTION

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. TERMINAL/CONTACT MATERIAL: SILVER PLATED
5. RATING: 3A @ 250VAC
6. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
7. ELECTRICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD
8. ACTUATOR FORCE: 1 POLES (SP) 2.5 ± 1.0 N
9. MECHANICAL LIFE: 1,000,000 (MOMENTARY) CYCLES
10. INSULATION RESISTANCE: 1,000M Ω @ 500VDC MIN.
11. DIELECTRIC STRENGTH: 2,000 RMS @ SEA LEVEL
12. OPERATING TEMPERATURE: -20°C to 55°C
13. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 14. LAMP VOLTAGE: 3V
15. TRAVEL: 3.2mm
16. MOUNTING NUT TORQUE: 0.3 - 0.5Nm
17. INGRESS PROTECTION: IP65
18. HARDWARE SUPPLIED: GASKET and MOUNTING NUT



 E-SWITCH®

OBJECT ID
100124728

TITLE LB22F2BQ6541

SCALE 1:1 DATE 5/19/2023 DR JS DWG T942009

REV A