



CIRCUIT: SPDT
CONTACT CONFIGURATION



SWITCH FUNCTION			
PDS. 1	PDS. 2	PDS. 3	
DN	NONE	DN	
2-3	OPEN	2-1	

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 5A @120VAC or 28VDC
2A @250VAC
5. FIXED TERM. & MOVING CONTACT:
Copper Alloy W/SILVER plate
6. ELECTRICAL LIFE: 50,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000M ohm min.
8. DIELECTRIC STRENGTH: 1,000V RMS @sea level.
9. OPERATING TEMP.: -30°C to +85°C.
10. 2002/95/EC (ROHS) COMPLIANT



RECOMMENDED P.C.B. LAYOUT



F	15899	DIM FROM 9.14 TO 8.65	3/27/06	PH	E-SWITCH® TITLE100 SP-1 T1 B1 M6 Q E SCALE2:1DATE4/9/02DRCJBDWG T111014REV F			
E	15537	DIM FROM 8.89 TO 8.40	11/16/05	PH				
D	15503	ADD ROHS NOTE	11/7/05	PH				
C	12046	REVISED AND REDRAWN	4/9/02	CJB				
REV.	ECN No.	DESCRIPTION	DATE	CHKD				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED								