






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. RATING: 20VDC @ 1mA
4. CONTACT RESISTANCE: 200Ω MAX.
5. INSULATION RESISTANCE: 100MΩ MIN. @ 100VDC.
- ▲ 6. OPERATING FORCE: 125± 35gf
7. TRAVEL: 1.3 +/- 0.3 mm
8. OPERATING TEMPERATURE: -40°C TO 85°C
9. OPERATING LIFE: 1,000,000 CYCLES
- ▲ 10. LED: GREEN
11. ▲ DENOTES CRITICAL PARAMETERS
12. CONTACT MATR'L: GOLD FLASH OVER NICKEL



LED SPECS	UNITS	GREEN	
FORWARD CURRENT	mA	20	
FORWARD VOLTAGE @20mA	V	2.1 TYP	2.5 MAX
LUMINOUS INTENSITY @ 20mA	mcd	50 TYP	

REV	ECO NO	DESCRIPTION	DATE	BY	 OBJECT ID 000006814				
C	ECO-101243	UPDATE TO CURRENT LED SPECS	09/22/22	JS					
					TITLE LP15S1BLKGRNN				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 2:1	DATE 10/17/2011	DR BGL	DWG B270006	REV C