








PCB LAYOUT



▲ CIRCUIT DIAGRAM




NO ACTUATOR CAP



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: CURRENT: 100mA
VOLTAGE: 30 VDC
5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 500VDC, 100MΩ. MIN.
7. OPERATING FORCE: 250gf $\pm$ 100 GRAMS
8. OPERATING TEMP.: -40°C to 85°C
- ▲ 9. TRAVEL: LATCHING
1.80 $\pm$ 0.3mm FULL TRAVEL
10. CONTACT RESISTANCE: 50 mΩ. MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (ROHS) COMPLIANT
- ▲ 13. LED COLOR: NO LED



TITLE LP4EE1PBNNN

A	22252	RELEASE FOR PRODUCTION	4/7/16	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 2:1

DATE 4/6/2016

DR MW

DWG B240054

REV A