







NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: CURRENT: 100mA
VOLTAGE: 30 VDC
5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 500VDC, 100M Ω . MIN.
7. OPERATING FORCE: 250gf $\pm$ 100 GRAMS
8. OPERATING TEMP.: -40°C to 85°C
- ▲ 9. TRAVEL: LATCHING
1.80 $\pm$ 0.3mm FULL TRAVEL
10. CONTACT RESISTANCE: 50 m Ω . MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (ROHS) COMPLIANT
- ▲ 13. LED COLOR: YELLOW



NO ACTUATOR CAP



LED SPECS	UNITS	YELLOW
FORWARD CURRENT	mA	20
FORWARD VOLTAGE	V	2.0-2.5
LUMINOUS INTENSITY	MCD	200



TITLE LP4EE1PBNNY

SCALE 2:1

DATE 4/6/2016

DR MW

DWG B240057

REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

A	22252	RELEASE FOR PRODUCTION	4/8/16	MW
REV	PCR NO	DESCRIPTION	DATE	BY