






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: CURRENT: 100mA
VOLTAGE: 30 VDC
5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 500VDC, 100MΩ MIN.
7. OPERATING FORCE: 250gf \pm 100 GRAMS
8. OPERATING TEMP.: -20°C to 70°C
9. TRAVEL: 1.00 ± 0.3 mm LOCK
▲ 1.50 ± 0.3 mm FULL TRAVEL
10. CONTACT RESISTANCE: 50 mΩ MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (ROHS) COMPLIANT
13. LED COLOR: RED



LED SPECS	UNITS	RED
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	1.9-2.5
LUMINOUS INTENSITY @ 10mA	MCD	200

E-SWITCH®

A	21144	RELEASE FOR PRODUCTION	5/31/13	EBP	TITLE	LP4EE1PGCTR			
REV	PCR NO	DESCRIPTION	DATE	BY					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV
						5/31/2013	EBP	B240050	A