






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: CURRENT: 100mA
VOLTAGE: 30 VDC
5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 500VDC, 100M OHM. MIN.
7. OPERATING FORCE: 250 ± 100 gf
8. OPERATING TEMP.: -40°C to 85°C
- ▲ 9. TRAVEL: MOMENTARY
1.50 ± 0.3 mm FULL TRAVEL
10. CONTACT RESISTANCE: 50m OHM. MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LED COLOR: YELLOW



LED SPECS	UNITS	YELLOW
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @20mA	V	1.6-2.5
LUMINOUS INTENSITY @ 10mA	MCD	200 TYP

REV	ECO NO	DESCRIPTION	DATE	BY
F	ECO-103742	TEMP CHANGE -40 TO 85C	10/28/25	JS



E-SWITCH®

OBJECT ID
000006699TITLE
LP40A1RBTATYSCALE
2:1DATE
5/18/2010DR
rcDWG
B240039REV
FTHE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED