


CIRCUIT: SPST
CONTACT CONFIGURATION

SWITCH FUNCTION		
PDS. 1	PDS. 2	PDS. 3
		
OFF	NONE	ON
OPEN	NA	3-1

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
- ▲ 4. CONTACT RATING: 3 AMPS @ 120VAC OR 28VDC;
1 AMPS @ 250VAC
5. FIXED TERMINAL & MOVING CONTACT:
Cu alloy w/SILVER plate over Nickel.
6. ELECTRIC LIFE: 30,000 make-and-break cycles
at full load.
7. INSULATION RESISTANCE: 1,000 M ohm min.
8. DIELECTRIC STRENGTH: 1,000 V RMS @sea level.
9. OPERATING TEMP.: -30°C to +85°C
10. PACKAGE: TRAY/63 PIECES PER TRAY
11. 2002/95/EC (ROHS) COMPLIANT

RECOMMENDED P.C.B. LAYOUT



B	17419	REMOVED MIDDLE TERMINAL	6/27/07	TN
A	17328	RELEASED FOR PRODUCTION	5/30/07	TN
REV.	ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

				
TITLE				
400MSP6R6BLKM7QE				
SCALE	DATE	DR	DWG	REV
2:1	6/27/07	TN	T416068	B