




SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
1-3	1-2

(ON) = MOMENTARY



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: SILVER
5. CONTACT RESISTANCE: 20 mΩ MAX.
6. RATING: 3A @ 120VAC or 28VDC; 1A @ 250VAC
7. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
8. MECHANICAL LIFE: 50,000 CYCLES
9. INSULATION RESISTANCE: 1,000 MΩ MIN.
10. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
11. OPERATING TEMP.: -40°C to 85°C
12. INGRESS PROTECTION: IP67
13. ▲ DENOTES CRITICAL PARAMETER.
14. HARDWARE TO BE SHIPPED BULK
T100000 - HEXNUT - QTY 2
T100011 - LOCKWASHER - QTY 1
T100015 - LOCKRING - QTY 1



REV	ECO NO	DESCRIPTION	DATE	BY
E	ECO-103072	700A SERIES UPDATE	11/22/24	JS



OBJECT ID
000023388

TITLE 700ASP7B10M6QEH		SCALE 2:1	DATE 11/7/2007	DR BLR	DWG ST750102	REV E
--------------------------	--	--------------	-------------------	-----------	-----------------	----------