



| SWITCH FUNCTION | |
|-----------------|--------|
| POS. 1 | POS. 2 |
| | |
| ON | (ON) |
| 1-3 | 1-2 |

(ON) = MOMENTARY



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: SILVER
5. CONTACT RESISTANCE: 20 mΩ MAX.
6. RATING: 3A @ 120VAC OR 28VDC
1A @250VAC
7. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
Min. AT FULL LOAD.
8. MECHANICAL LIFE: 50,000 CYCLES
9. INSULATION RESISTANCE: 1,000 MΩ MIN.
10. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
11. INGRESS PROTECTION: IP67
12. OPERATING TEMP.: -40°C to 85°C
13. ▲ DENOTES CRITICAL PARAMETER.

| REV | ECO NO | DESCRIPTION | DATE | BY | E-SWITCH® | | | OBJECT ID | |
|-----|------------|--------------------|----------|----|----------------------|-----------|-----|-----------|-----|
| B | ECO-103090 | 700A SERIES UPDATE | 11/25/24 | JS | | | | 000025814 | |
| | | | | | TITLE 700ASP7B10M7QE | | | | |
| | | | | | SCALE | DATE | DR | DWG | REV |
| | | | | | BLR | 3/14/2008 | 2:1 | T750104 | B |