






SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
1-3, 4-6	1-2, 4-5

(ON)=MOMENTARY



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 1A @ 250 VAC
3A @ 120 VAC OR 28 VDC MAX.
6. ELECTRIC LIFE: 6,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD
7. MECHANICAL LIFE: 50,000 CYCLES
8. INSULATION RESISTANCE: 1,000 MΩ MIN.
- ▲ 9. ACTUATION FORCE: 800 ± 200gf
10. TRAVEL: 1.0 ± 0.2mm
11. CONTACT RESISTANCE: 20 mΩ MAX.
TYPICAL @ 2-4 VDC
12. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL.
13. OPERATING TEMP.: -40°C to 85°C
14. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®				OBJECT ID
C	ECO-102897	700 SERIES UPDATE	09/03/24	JS	TITLE 700DP7B11M1QE				000025768
					SCALE 2:1	DATE 5/10/2011	DR BGL	DWG T711085	REV C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED