







SWITCH FUNCTION

POS. 1	POS. 2
	
ON	(ON)
1-3	1-2



(ON)=MOMENTARY



CIRCUIT: SPDT

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: GOLD PLATED
5. RATING: 0.4VA @ 20 VAC OR VDC MAX.
6. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD
7. MECHANICAL LIFE: 50,000 CYCLES
8. INSULATION RESISTANCE: 1,000 M Ω MIN.
- ▲ 9. ACTUATION FORCE: 350 $\pm$ 150gf
10. TRAVEL: 1.0 $\pm$ 0.2mm
11. CONTACT RESISTANCE: 20 m Ω MAX.
TYPICAL @ 2-4 VDC
12. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL.
13. OPERATING TEMP.: -40°C to 85°C
14. ▲ DENOTES CRITICAL PARAMETER.
15. HARDWARE TO BE SHIPPED BULK
T100000 - HEXNUT - QTY 2
T100011 - LOCKWASHER - QTY 1
T100015 - LOCKRING - QTY 1



REV	ECO NO	DESCRIPTION	DATE	BY	 OBJECT ID 000023354				
C	ECO-102819	700 SERIES UPDATE	08/05/24	JS					
					TITLE 700SP7B10VS5REH				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 2:1	DATE 8/23/2006	DR BO	DWG ST711052	REV C