







O.P. (MM)	P.T. (MM)
10.9±1.0	3.2 MAX.



O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



SCHEMATIC - SPDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. RATING: 5A @125/250VAC UL, CUL
- ▲ 4. OPERATING FORCE: 060± 25 GRAMS
5. OPERATING TEMP: -25°C to 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI-OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. 270 PCS PER CASE/14 CASES PER BOX.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®					OBJECT ID
C	ECO-100777	REMOVE VDE RATING AND LOGO	03/14/22	JS						000021207
					TITLEMS0850504F060V2A					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 2:1	DATE 3/1/2007	DR TN	DWG Q970071	REV C	