







P.C. MOUNTING



O.P. (MM)	P.T. (MM)
14.9 ± 1.0	4.0 MAX


O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



SCHEMATIC - SPDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- ▲ 3. RATING: 5A @125/250VAC UL, CUL
- ▲ 4. OPERATING FORCE: 75 ± 25 gf
5. OPERATING TEMP: -25°C to 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITAL VALUE)
10. CONTACT RESISTANCE: 100 m Ω MAX.
- ▲ 11. CONTACT MATERIAL: SILVER
12. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®					OBJECT ID
A	ECO-100762	Release	02/28/22	MW						100121348
					TITLE MS0850505F075V1A					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 2:1	DATE 2/24/2022	DR MW	DWG Q970186	REV A	