









| SWITCH FUNCTION |        |
|-----------------|--------|
| POS. 1          | POS. 2 |
|                 |        |
| ON              | (ON)   |
| 1-3             | 1-2    |

(ON) = MOMENTARY



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: GOLD
5. RATING: 0.4 VA MAX. @ 20 VAC OR VDC MAX.
6. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES  
AT FULL LOAD
7. MECHANICAL LIFE: 50,000 CYCLES
8. INSULATION RESISTANCE: 1,000 MΩ MIN.
9. ACTUATION FORCE: 350 ± 150gf
10. TRAVEL: 1.0 ± 0.2mm
11. CONTACT RESISTANCE: 20 mΩ MAX.  
TYPICAL @ 2-4 VDC
12. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL.
13. OPERATING TEMP.: -40°C to 85°C
14. ▲ DENOTES CRITICAL PARAMETER.



| REV | ECO NO     | DESCRIPTION       | DATE     | BY | E-SWITCH®           |          |    |         | OBJECT ID |
|-----|------------|-------------------|----------|----|---------------------|----------|----|---------|-----------|
| D   | ECO-102768 | 700 SERIES UPDATE | 06/06/24 | JS | TITLE 700SP7B11M6RE |          |    |         | 000025752 |
|     |            |                   |          |    | SCALE               | DATE     | DR | DWG     | REV       |
|     |            |                   |          |    | 2:1                 | 8/9/2006 | BO | T711066 | D         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED