






SWITCH FUNCTION	
POS. 1	POS. 2
	
ON	(ON)
1-3	1-2

() = MOMENTARY



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A @ 120 VAC OR 28 VDC
1A @ 250 VAC
6. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD
7. MECHANICAL LIFE: 50,000 CYCLES
8. INSULATION RESISTANCE: 1,000 M Ω MIN.
- ▲ 9. ACTUATION FORCE: 350 $\pm$ 150gf
10. TRAVEL: 1.0 $\pm$ 0.2mm
11. CONTACT RESISTANCE: 20 m Ω MAX.
TYPICAL @ 2-4 VDC
12. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL.
13. OPERATING TEMP.: -40°C to 85°C
14. ▲ DENOTES CRITICAL PARAMETER.
15. HARDWARE TO BE SHIPPED BULK:
T100011 - LOCK WASHER, QTY 1
T100002 - LOCK RING, QTY 1
T100000 - HEX NUT, QTY 2



REV	ECO NO	DESCRIPTION	DATE	BY	 OBJECT ID 000023350				
D	ECO-102768	700 SERIES UPDATE	08/19/24	JS					
					TITLE 700SP7B11M7QEH				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 2:1	DATE 8/29/2003	DR AR	DWG ST711045	REV D