






SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-3

(ON)=MOMENTARY



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 - ▲ 4. CONTACTS/TERMINALS: SILVER PLATED
 5. RATING: 1A @ 250 VAC
3A @ 120 VAC or 28 VDC
 6. ELECTRICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
 7. MECHANICAL LIFE: 50,000 MAKE-AND-BREAK CYCLES
 8. CONTACT RESISTANCE: 20m Ω MAX. INITIAL @ 2-4VDC 100mA
 9. INSULATION RESISTANCE: 1,000M Ω MIN.
 10. DIELECTRIC STRENGTH: 1,000 V RMS @ SEA LEVEL
 11. OPERATING TEMP.: -40°C to 85°C
 12. ▲ DENOTES CRITICAL PARAMETER.
 - ▲ 13. HARDWARE INCLUDED: T100000 - HEXNUT (2)
T100011 - LOCKWASHER (1)
T100002 - LOCKRING (1)



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®					OBJECT ID	
D	ECO-103157	Release	12/30/24	MW						000023406	
					TITLE 800SP9B9M1QEH						
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV		
					2:1	6/14/2011	BMA	ST811050	D		