





P.C. MOUNTING

O.P. (MM)	P.T. (MM)
14.9±1.0	4.0 MAX





O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



SCHEMATIC SPDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X±0.4
X.XX±0.25
3. RATING: 0.4VA @20VAC OR DC
- ▲ 4. OPERATING FORCE: 45±20 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES
7. MECHANICAL LIFE: 1,000,000 CYCLES
9. INSULATION RESISTANCE: 100 MEGA-OHMS
9. DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 mΩ MAX.
- ▲ 11. CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (PN: Q990001)
12. ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100792	REMOVE VDE RATING AND LOGO	03/23/22	JS	TITLE MS085R105F045V1A				000021272
					SCALE	DATE	DR	DWG	REV
					2:1	9/18/2013	EBP	Q970136	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED