






RECOMMENDED PANEL MOUNTING



- NOTE:
1. ALL DIMENSIONS IN MM [INCH].
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERMINAL NUMBERS FOR REF ONLY.
 - ▲ 4. CONTACT RATING: 5A @ 250VAC,
8A @ 125VAC,
6A @ 24VDC
 5. ELECTRICAL LIFE: 50,000 OPERATIONS
 6. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
 - ▲ 7. CONTACT MATERIAL: SILVER PLATED COPPER ALLOY
 8. ACTUATION FORCE: 300g / POLE
 9. OPERATING TEMP.: -25°C to +55°C
 10. ▲ DENOTES CRITICAL PARAMETER.
 11. 2002/95/EC (ROHS) COMPLIANT

| PARTS LIST | | | |
|------------|-----|-------------|----------------------------------|
| ITEM | QTY | PART NUMBER | DESCRIPTION |
| 1 | 1 | F040009 | D160AR11 |
| 2 | 1 | F050102 | 50-001-02 TRANSPARENT GREEN LENS |
| 3 | 1 | F050419 | 50-004-19M GREEN LED 12 VDC |



| REV | PCR NO | DESCRIPTION | DATE | BY |
|-----|--------|---------------------------|----------|-----|
| C | 20382 | CHANGE LED DESCRIPTION | 01/05/12 | BMA |
| B | 19783 | DRAWING CLEAN UP / UPDATE | 3/22/11 | BGL |

| | | | | |
|------------------------------|-----------|-----|---------|-----|
| TITLE D160AR11JGRNGRN | | | | |
| SCALE | DATE | DR | DWG | REV |
| 1.5:1 | 3/22/2011 | BGL | XF0310P | C |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED