






RECOMMENDED PANEL CUTOUT



CIRCUIT DIAGRAM



NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NUMBERS FOR REFERENCE ONLY.
4. CONTACT RATING: 0.2A @ 30VDC
5. TRAVEL: 3.0 mm
6. OPERATING FORCE: 200 ± 100 gf
7. LIFE EXPECTANCY: 10,000 CYCLES
8. OPERATING TEMP: -20°C to 70°C
9. ▲ DENOTES CRITICAL PARAMETER
10. 2011/65/EU (ROHS) COMPLIANT



TITLE EG1201A (SOLDER LUG, NON-SHORTING)

C	23226	Drawing updated and redrawn	2/20/18	MW			
REV	PCR NO	DESCRIPTION	DATE	BY	SCALE	DATE	DR DWG
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					2:1	2/20/2018	MW P040011