







PANEL THICKNESS	X ± 0.05mm
0.75-1.25mm	19.15mm
1.25-2.00mm	19.35mm
2.00-3.00mm	19.55mm

SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)
OPEN	1-2, 3-4

(ON) = MOMENTARY



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. MECHANICAL LIFE: 30,000
4. ELECTRICAL LIFE: 10,000
5. CONTACT RESISTANCE: 20 mILLI OHMS
6. INSULATION RESISTANCE: 1000 MEGA OHMS
7. OPERATING TEMPERATURE: -10°C TO 55°C
8. CONTACT RATING: 15A 250VAC, 125VAC UL
10A 250VAC, VDE
9. DIELECTRIC STRENGTH: 1500V FOR 1 MIN
- ▲ 10. LAMP: LED, 12VDC
11. ▲ DENOTES CRITICAL PARAMETER
12. OPERATING FORCE: 1000±100grams

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
E	ECO-103805	LAMP TO LED	12/15/25	JS	PB1973HBLKGILEF3				000016524
					SCALE	DATE	DR	DWG	REV
					3:2	9/27/2007	BF	M197302	E

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED