





E-SWITCH LOGO-



1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING 0.1A @30V DC
- ▲ 5. MATERIALS:

CONTACT/TERMINALS: SILVER PLATE
HOUSING: PBT UL94V0
BASE: PA66 UL94V0
ACTUATOR: PA66 UL94V0

6. CONTACT RESISTANCE: 100 mΩ (INITIAL) ▲
7. TIMING: NON-SHORTING
8. OPERATING FORCE: 230± 50GF
9. TRAVEL: MOMENTARY; 3MM OVERALL
10. ELECTRICAL LIFE: 10000 CYCLES
11. OPERATING TEMP: -20°C TO +70°C
12. ▲ DENOTES CRITICAL PARAMETER.
13. 2002/95/EC (ROHS) COMPLIANT



D	19670	CIRCUIT DIAGRAM & DIM CHANGES	2/10/11	BGL
C	15671	ADD CRITICAL TO 2.50 DIM	1/10/06	PH
B	15553	ADD PBH FRONT, DIM FROM 7.00 TO 7.30	11/21/05	PH
A	15376	RELEASED FOR PRODUCTION	10/12/05	PH
REV	PCR NO	DESCRIPTION	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				

									
TITLE PBH2UOASNPNAV									
SCALE	2.5:1	DATE	10/12/2005	DR	PH	DWG	Q960013	REV	D