








## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING 0.1A @30V DC
- ▲ 5. MATERIALS:  
CONTACT/TERMINALS: SILVER PLATE  
HOUSING: PBT UL94HB  
BASE: PA66 UL94HB  
ACTUATOR: POM
6. CONTACT RESISTANCE: 100 MILLI-OHM (INITIAL)
- ▲ 7. TIMING: NON-SHORTING
8. OPERATING FORCE:  $230 \pm 50\text{gf}$
9. TRAVEL: MOMENTARY  
3mm OVERALL, 2mm to MAKE
10. ELECTRICAL LIFE: 10,000 CYCLES
11. OPERATING TEMP:  $-20^{\circ}\text{C}$  to  $+70^{\circ}\text{C}$
12. ▲ DENOTES CRITICAL PARAMETER.



|     |        |                         |        |    |
|-----|--------|-------------------------|--------|----|
| A   | 23532  | RELEASED FOR PRODUCTION | 9/4/18 | MW |
| REV | PCR NO | DESCRIPTION             | DATE   | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PBH2UOASNPAGX

|              |                  |          |                |          |
|--------------|------------------|----------|----------------|----------|
| SCALE<br>2:1 | DATE<br>9/4/2018 | DR<br>MW | DWG<br>Q960036 | REV<br>A |
|--------------|------------------|----------|----------------|----------|