




RECOMMENDED
PANEL CUT-OUT
1-6mm THICKNESS



SWITCH FUNCTION	
POS. 1	POS. 2
OFF	(ON)

OPEN 1-2
(ON) = MOMENTARY



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. RATING: 2A @ 36VDC
5. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
6. INSULATION RESISTANCE: 1,000MΩ @ 500VDC
7. DIELECTRIC STRENGTH: 2,000VAC MIN. FOR 1 MINUTE
8. ELECTRICAL LIFE: 200,000 CYCLES
9. CONTACT MATERIAL: GOLD
10. OPERATING TEMPERATURE: -20°C to 55°C
11. INGRESS PROTECTION: IP65
12. LED VOLTAGE: BASE VOLTAGE 1.8V TYP.
13. ▲ DENOTES CRITICAL PARAMETER
14. HARDWARE INCLUDED: HEX NUT and O-RING (NOT SHOWN)

B	24583	HOUSING UPDATE	11/9/20	JM
A	24357	RELEASE	6/22/20	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

 E-SWITCH® OBJECT ID 000002291				
TITLE		PV0H24011G-211		
SCALE	2:1	DATE	6/22/2020	DR MW DWG 52-PV0H24011G211 REV B