









NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 100mA
5. CONTACT MATERIAL: GOLD PLATED
6. CONTACT RESISTANCE: 200 mΩ MAX.
7. INSULATION RESISTANCE: 500VDC, 100 MΩ MIN.
8. OPERATING FORCE: 200 ± 80gf
9. MECHANICAL LIFE: 2,000,000 CYCLES
10. OPERATING TEMP: -40°C to +85°C
- ▲ 11. LED COLORS: GREEN / WHITE
12. TRAVEL: 4.50mm ±0.20mm
13. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 14. SWITCH HAS NON TACTILE FEEDBACK WHEN ACTUATED



LED SPECS	UNITS	GREEN	WHITE
FORWARD CURRENT	mA	20	20
FORWARD VOLTAGE @20mA	V	2.7-4.1	2.8-4.0
LUMINOUS INTENSITY @20mA	MCD	200-700	120-400



E-SWITCH®

B	24793	updated notes and LED specs	3/9/21	MW
A	24751	RELEASE	2/23/21	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE LP110A1NCSGW

SCALE 3:2

DATE 2/24/2021

DR MW

DWG B231024

REV B