






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: CURRENT: 100mA
VOLTAGE: 30 VDC
5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 500VDC, 100M OHM. MIN.
7. OPERATING FORCE: 250gf ± 100 gf
8. OPERATING TEMP.: -20°C to 70°C
- ▲ 9. TRAVEL: LATCHING
1.50 ± 0.3 mm FULL TRAVEL
10. CONTACT RESISTANCE: 50m OHM. MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LED COLOR: YELLOW

YELLOW CAP
with YELLOW LED

LED SPECS	UNITS	YELLOW
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @ 20mA	V	1.7-2.4
LUMINOUS INTENSITY @ 10mA	MCD	350

REV	ECO NO	DESCRIPTION	DATE	BY
A	ECO-100552	Release	11/18/21	MW



E-SWITCH®

OBJECT ID
100120024TITLE
LP4EE1PBBYYSCALE
2:1DATE
11/12/2021DR
MWDWG
B240067REV
ATHE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED