







NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT RATING: CURRENT: 100mA
VOLTAGE: 30 VDC
5. OPERATING LIFE: 50,000 MAKE-AND-BREAK CYCLES
6. INSULATION RESISTANCE: 500VDC, 100M Ω MIN.
7. OPERATING FORCE: 250gf $\pm$ 100gf
8. OPERATING TEMP.: -40°C to 85°C
- ▲ 9. TRAVEL: 0.7 $\pm$ 0.3mm LOCK
1.8 $\pm$ 0.3mm FULL TRAVEL
10. CONTACT RESISTANCE: 50m Ω MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 12. LED COLOR: WHITE



TRANSPARENT BLUE CAP
w/o BEZEL
with WHITE LED



LED SPECS	UNITS	WHITE
FORWARD CURRENT	mA	20
FORWARD VOLTAGE @ 20mA	V	3.2 - 4.0
LUMINOUS INTENSITY @ 20mA	MCD	250

REV	ECO NO	DESCRIPTION	DATE	BY
A	ECO-101016	Release	06/02/22	MW



E-SWITCH®

OBJECT ID
100122083

TITLE	LP4EE1PBCBW
-------	-------------

SCALE
2:1

DATE	5/26/2022
------	-----------

DR	MW
----	----

DWG B240069

REV
A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED