



SCHEMATIC
ON - (ON)
() = MOMENTARY
SPDT NON -ILLUMINATED




RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS 8.0 [.31 in]

SWITCH	WIRE	LENGTH
SW1-1	WIRE, 22AWG AWM UL1007, YELLOW	300.0 [11.8 in]
SW1-2	WIRE, 22AWG AWM UL1007, BLUE	300.0 [11.8 in]
SW1-3	WIRE, 22AWG AWM UL1007, GREEN	300.0 [11.8 in]



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: GOLD
5. RATING: 2A 48VDC
6. LAMP VOLTAGE: N/A
7. INGRESS RATING: IP40
8. ILLUMINATION COLOR: N/A
9. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
10. INSULATION RESISTANCE: 1,000 MΩ MIN.
11. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
12. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
13. OPERATING TEMP.: -20°C to 55°C
14. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 15. HARDWARE: O-RING AND HEXNUT SUPPLIED.
- ▲ 16. USE PART NUMBERS DESIGNATED OR ENGINEERING APPROVED EQUIVALENTS.



TITLE PV3SGWB0BBG

A	23981	RELEASE	8/2/19	MW
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 2:3	DATE 8/2/2019	DR MW	DWG 52-PV3SGWB0BBG	REV A
--------------	------------------	----------	-----------------------	----------