








| O.P. (MM) | P.T. (MM) |
|-----------|-----------|
| 14.7±0.5  | 2.0 MAX.  |

O.P. = OPERATING POINT  
P.T. = PRE-TRAVEL



## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X±0.4  
X.XX±0.25
3. RATING: 15A @125/250VAC UL, CUL APPROVED
- ▲ 4. OPERATING FORCE: 250±50 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.

| REV | ECO NO     | DESCRIPTION          | DATE     | BY | E-SWITCH®              |           |     |         | OBJECT ID |
|-----|------------|----------------------|----------|----|------------------------|-----------|-----|---------|-----------|
| C   | ECO-102246 | P.T. 2.0 MAX WAS 1.5 | 09/27/23 | JS | TITLE LS0851500F250V2A |           |     |         | 000021039 |
|     |            |                      |          |    | SCALE                  | DATE      | DR  | DWG     | REV       |
|     |            |                      |          |    | 3:2                    | 4/25/2008 | BLR | Q950052 | C         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED