


RECOMMENDED PANEL CUTOUT
MAX. PANEL THICKNESS
11.0 [.43 in]


SWITCH FUNCTION	
POS. 1	POS. 2
ON	ON
1-3, 4-6	1-2, 4-5



WHITE (REVERSE)
(+) (-)
WHITE (FORWARD)

▲ DPDT
CONTACT CONFIGURATION

Ø22.00
[.866 in]
Ø15.8
[Ø.62 in]
Ø13.6
[Ø.54 in]




▲ RING
ILLUMINATION COLOR:
WHITE

▲ FLAT
ACTUATOR FINISH:
BLACK ANODIZED



1.8
[.07 in]

28.7±1.0
[1.13±.04 in]





▲ BODY FINISH:
BLACK ANODIZED

▲ 37.8±1.0
[1.49±.04 in]

10.00
[.394 in]

2.80
[.110 in]



M19 X 1.0

3.60
[.142 in]
5.50
[.217 in]
12.00
[.472 in]

.50
[.020 in]

NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. RATING: 2A 24VDC
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MΩ MIN.
8. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
9. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
10. OPERATING TEMP.: -40°C TO 85°C
11. TRAVEL: 2.8 [.11 in]
12. ▲ DENOTES CRITICAL PARAMETER
13. INGRESS PROTECTION: IP67
14. HARDWARE SUPPLIED: O-RING AND HEXNUT
15. ILLUMINATION VOLTAGE: 2.8V WHITE

REV	ECO NO	DESCRIPTION	DATE	BY					OBJECT ID
D	ECO-103867	PV4 SERIES UPDATE	01/14/26	MR	TITLE PV4F2G011-311				000002642
					SCALE 1:1	DATE 8/5/2009	DR EBP	DWG 52-PV4F2G011311	REV D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED