


RECOMMENDED PANEL CUTOUT  
MAX. PANEL THICKNESS  
11.0 [.43 in]





| SWITCH FUNCTION |          |
|-----------------|----------|
| POS. 1          | POS. 2   |
|                 |          |
| ON              | (ON)     |
| 1-3, 4-6        | 1-2, 4-5 |

(ON) = MOMENTARY



## NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 2A 24VDC
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 M $\Omega$  MIN.
- DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- CONTACT RESISTANCE: 50m $\Omega$  MAX. @ 1A 12VDC
- OPERATING TEMP.: -40°C TO 85°C
- TRAVEL: 2.8 [.11 in]
- ▲ DENOTES CRITICAL PARAMETER
- INGRESS PROTECTION: IP67
- HARDWARE SUPPLIED: O-RING AND HEXNUT
- ILLUMINATION VOLTAGE: 2.8V



| REV | ECO NO     | DESCRIPTION       | DATE     | BY |
|-----|------------|-------------------|----------|----|
| B   | ECO-103867 | PV4 SERIES UPDATE | 01/14/26 | MR |
|     |            |                   |          |    |
|     |            |                   |          |    |



E-SWITCH®

OBJECT ID  
000002664

TITLE PV4F2H01S-341-M01

SCALE  
1:1

DATE  
6/17/2015

DR  
MW

DWG  
52-PV4F2H01S341M01

REV  
B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO  
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED