


O.P. (MM)	P.T. (MM)
19.0 ± 1.5	5.2 MAX.





O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



CIRCUIT: SPDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. RATING: 0.4VA @20VAC OR DC
▲ 4. OPERATING FORCE: 50± 20 GRAMS
5. OPERATING TEMP: -25°C TO 85°C
6. ELECTRICAL LIFE: 50,000 CYCLES MIN.
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
9. DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
10. CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
11. ▲ DENOTES CRITICAL PARAMETER.
12. CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (P/N Q990000)



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®					OBJECT ID
D	ECO-102147	NOTE 4: 50+/-20 WAS 050+/-20	08/10/23	JS						000021021
					TITLE					LS085R104F050C1A
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV	
					3:2	2/23/2006	PH	Q950034	D	