









O.P. (MM)	P.T. (MM)
20.7 ± 0.8	1.90 MAX.

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
- RATING: 0.4VA @20VAC OR DC
- OPERATING FORCE: 160 ± 40 GRAMS
- OPERATING TEMP: -25°C TO 85°C
- ELECTRICAL LIFE: 50,000 CYCLES MIN.
- MECHANICAL LIFE: 1,000,000 CYCLES TYP.
- INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
- DIELECTRIC STRENGTH: 1500VAC 1 MINUTE (INITIAL VALUE)
- CONTACT RESISTANCE: 100 MILLI -OHMS MAX.
- ▲ DENOTES CRITICAL PARAMETER.
- CONTACTS: 10 MICRO INCHES MINIMUM GOLD PLATING (P/N Q990000)

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®		OBJECT ID	
B	ECO-100837	REMOVE VDE RATING AND LOGO	04/26/22	JS	TITLE LS085R105F160V1A		000021059	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	REV
					3:2	8/18/2009	BLR	B
					DWG		REV	
					Q950075		B	