


BLUE (FORWARD)




BLUE (REVERSE)

SCHEMATIC

ON - ON - DPDT ILLUMINATED

SWITCH	WIRE
SW1-1	WIRE, 24AWG AWM UL1015, YELLOW
SW1-2	WIRE, 24AWG AWM UL1015, BLUE
SW1-3	WIRE, 24AWG AWM UL1015, GREEN
SW1-4	WIRE, 24AWG AWM UL1015, PURPLE
SW1-5	WIRE, 24AWG AWM UL1015, ORANGE
SW1-6	WIRE, 24AWG AWM UL1015, WHITE
SW1- (+)	WIRE, 24AWG AWM UL1015, RED
SW1- (-)	WIRE, 24AWG AWM UL1015, BLACK






RECOMMENDED PANEL CUTOUT

MAX. PANEL THICKNESS 11.0 [.43 in]

NOTES:

- DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
- ALL MATERIAL SHALL BE ROHS COMPLIANT
- TERMINAL NUMBERS FOR REF. ONLY
- CONTACT MATERIAL: SILVER
- RATING: 2A 24VDC
- ▲ LAMP VOLTAGE: 2.8V BLUE
- INGRESS PROTECTION: IP67
- TRAVEL: 2.8 [.11 in]
- OPERATING TEMP.: -20°C TO 85°C
- INSULATION RESISTANCE: 1,000 MΩ MIN.
- CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
- DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- ▲ DENOTES CRITICAL PARAMETER.
- SUPPLIED HARDWARE: O-RING AND HEXNUT
- ▲ 17. USE PART NUMBERS DESIGNATED OR ENGINEERING APPROVED EQUIVALENTS.



BOTTOM VIEW
SHOWN WITHOUT
WIRING

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
E	ECO-103811	PV4 SERIES UPDATE	01/14/26	MR	TITLE PV4FWG0SS-341				000002750
					SCALE	DATE	DR	DWG	REV
					2:3	1/18/2019	MJR	52-PV4FWG0SS341	E

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED