





SCHEMATIC
 ON - (ON) - DPDT ILLUMINATED
 () DENOTES MOMENTARY FUNCTION



RECOMMENDED PANEL CUTOUT
 MAX. PANEL THICKNESS 11.0 [.43 in]

- NOTES:
1. DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X = ± 0.4
 $X.XX = \pm 0.25$
 3. ALL MATERIAL SHALL BE ROHS COMPLIANT
 4. TERMINAL NUMBERS FOR REF. ONLY
 5. CONTACT MATERIAL: SILVER
 6. RATING: 2A 24VDC
 7. LAMP VOLTAGE: 2.8V BLUE
 8. INGRESS PROTECTION: IP67
 9. TRAVEL: 2.8 [.11 in]
 10. OPERATING TEMP.: -20°C TO 85°C
 11. INSULATION RESISTANCE: 1,000 MΩ MIN.
 12. CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
 13. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
 14. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
 15. ▲ DENOTES CRITICAL PARAMETER.
 16. SUPPLIED HARDWARE: O-RING AND HEXNUT
 17. USE PART NUMBERS DESIGNATED OR ENGINEERING APPROVED EQUIVALENTS.

SWITCH	WIRE
SW1-1	WIRE, 24AWG AWM UL1015, YELLOW
SW1-2	WIRE, 24AWG AWM UL1015, BLUE
SW1-3	WIRE, 24AWG AWM UL1015, GREEN
SW1-4	WIRE, 24AWG AWM UL1015, PURPLE
SW1-5	WIRE, 24AWG AWM UL1015, ORANGE
SW1-6	WIRE, 24AWG AWM UL1015, WHITE
SW1- (+)	WIRE, 24AWG AWM UL1015, RED
SW1- (-)	WIRE, 24AWG AWM UL1015, BLACK



BOTTOM VIEW
 SHOWN WITHOUT
 WIRING

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®			OBJECT ID
E	ECO-103811	PV4 SERIES UPDATE	01/14/26	MR				000002752
					TITLE PV4FWH0SS-341			
					SCALE 2:3			
		THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED	DATE	1/18/2019	DR	MJR	DWG	52-PV4FWH0SS341
					REV			E